













P1F-S, ISO Profile & Tie Rod Cylinder, Cushions and Magnetic Piston Included					
STROKE (mm)	32mm BORE	40mm BORE	50mm BORE	63mm BORE	80mm BORE
25	P1F-S032MC-0025-0000 STEP PDF	P1F-S040MC-0025-0000 STEP PDF	P1F-S050MC-0025-0000 STEP PDF	P1F-S063MC-0025-0000 STEP PDF	P1F-S080MC-0025-0000 STEP PDF
40	P1F-S032MC-0040-0000 STEP PDF	P1F-S040MC-0040-0000 STEP PDF	P1F-S050MC-0040-0000 STEP PDF	P1F-S063MC-0040-0000 STEP PDF	P1F-S080MC-0040-0000 STEP PDF
50	P1F-S032MC-0050-0000 STEP PDF	P1F-S040MC-0050-0000 STEP PDF	P1F-S050MC-0050-0000 STEP PDF	P1F-S063MC-0050-0000 STEP PDF	P1F-S080MC-0050-0000 STEP PDF
80	P1F-S032MC-0080-0000 STEP PDF	P1F-S040MC-0080-0000 STEP PDF	P1F-S050MC-0080-0000 STEP PDF	P1F-S063MC-0080-0000 STEP PDF	P1F-S080MC-0080-0000 STEP PDF
100	P1F-S032MC-0100-0000 STEP PDF	P1F-S040MC-0100-0000 STEP PDF	P1F-S050MC-0100-0000 STEP PDF	P1F-S063MC-0100-0000 STEP PDF	P1F-S080MC-0100-0000 STEP PDF
125	P1F-S032MC-0125-0000 STEP PDF	P1F-S040MC-0125-0000 STEP PDF	P1F-S050MC-0125-0000 STEP PDF	P1F-S063MC-0125-0000 STEP PDF	P1F-S080MC-0125-0000 STEP PDF
160	P1F-S032MC-0160-0000 STEP PDF	P1F-S040MC-0160-0000 STEP PDF	P1F-S050MC-0160-0000 STEP PDF	P1F-S063MC-0160-0000 STEP PDF	P1F-S080MC-0160-0000 STEP PDF
200	P1F-S032MC-0200-0000 STEP PDF	P1F-S040MC-0200-0000 STEP PDF	P1F-S050MC-0200-0000 STEP PDF	P1F-S063MC-0200-0000 STEP PDF	P1F-S080MC-0200-0000 STEP PDF
250	P1F-S032MC-0250-0000 STEP PDF	P1F-S040MC-0250-0000 STEP PDF	P1F-S050MC-0250-0000 STEP PDF	P1F-S063MC-0250-0000 STEP PDF	P1F-S080MC-0250-0000 STEP PDF
320	P1F-S032MC-0320-0000 STEP PDF	P1F-S040MC-0320-0000 STEP PDF	P1F-S050MC-0320-0000 STEP PDF	P1F-S063MC-0320-0000 STEP PDF	P1F-S080MC-0320-0000 STEP PDF
400	P1F-S032MC-0400-0000 STEP PDF	P1F-S040MC-0400-0000 STEP PDF	P1F-S050MC-0400-0000 STEP PDF	P1F-S063MC-0400-0000 STEP PDF	P1F-S080MC-0400-0000 STEP PDF

BOLT ON MOUNTING BRACKETS						ACCESSORIES	
P1F Bore Size:	32 mm Bore	40 mm Bore	50 mm Bore	63 mm Bore	80 mm Bore		

	MF1 / MF2 FLANGE	P1C-4KMB	P1C-4LMB	P1C-4MMB	P1C-4NMB	P1C-4PMB	<p>AP6 SWIVEL ROD EYE</p>  <p>Part # P1C-4KRS Bore sizes: 32mm</p> <p>Part # P1C-4LRS Bore sizes: 40mm</p> <p>Part # P1C-4MRS Bore sizes: 50mm, 63mm</p> <p>Part # P1C-4PRS Bore sizes: 80mm</p> <p>AP2 ROD CLEVIS</p>  <p>Part # P1C-4KRC Bore sizes: 32mm</p> <p>Part # P1C-4LRC Bore sizes: 40mm</p> <p>Part # P1C-4MRC Bore sizes: 50mm, 63mm</p> <p>Part # P1C-4PRC Bore sizes: 80mm</p>	
	MS1 FOOT BRACKET	P1C-4KMF	P1C-4LMF	P1C-4MMF	P1C-4NMF	P1C-4PMF		
	AB7 PIVOT BRACKET	P1C-4KMDB	P1C-4LMDB	P1C-4MMDB	P1C-4NMDB	P1C-4PMDB		
	MP6 SWIVEL EYE	P1C-4KMSB	P1C-4LMSB	P1C-4MMSB	P1C-4NMSB	P1C-4PMSB		
	MP2 CLEVIS BRACKET	P1C-4KMTB	P1C-4LMTB	P1C-4MMTB	P1C-4NMTB	P1C-4PMTB		
	MP4 CLEVIS BRACKET	P1C-4KMEB	P1C-4LMEB	P1C-4MMEB	P1C-4NMEB	P1C-4PMEB		
	AB6 CLEVIS BRACKET	P1C-4KMCB	P1C-4LMCB	P1C-4MMCB	P1C-4NMCB	P1C-4PMCB		
	CS7 PIVOT BRACKET, SWIVEL	P1C-4KMAF	P1C-4LMAF	P1C-4MMAF	P1C-4NMAF	P1C-4PMAF		
	JP1 3,4 POSITION FLANGE	P1E-6KB0	P1E-6LB0	P1E-6MB0	P1E-6NB0	P1E-6PB0		
	MT5, MT6 FLANGE TRUNNION	P1D-4KMYF	P1D-4LMYF	P1D-4MMYF	P1D-4NMYF	P1D-4PMYF		