

# Condition Monitoring Solutions

	SensoControl	Industrial Mobile and SensoNODE Blue	Industrial Edge and SensoNODE Gold	Industrial Cloud and SensoNODE Gold
<b>Primary Application</b>				
Wireless Continuous Remote Monitoring			√	√
Wireless Route-Based Monitoring		√		
Diagnostics	√	√		
<b>Communication Method</b>				
900 MHz Wireless			√	√
Bluetooth Low Energy (BLE)		√		
Wires	√			
<b>Key Features</b>				
Alert Notifications - Text, Email, In-System			√	√
In-Use Alarms		√	√	√
Export and Share Data	√	√	√	√
Recordings	√	√	√	√
View Historical Data			√	√
Configurable Dashboards		√		
Functions or Calculations	√	√		
Configurable Units of Measure	√	√	√	√
Multiple Visualizations	√	√		
Viewable on Multiple Devices		√*	√	√
Add Sensors Instantly	√	√	√	
Fastest Measurement Rate	1 millisecond**	1 second	750 milliseconds	20 seconds
Pressure Spike and Drop Capturing	√			
Synchronization of Measurement Inputs	√			
Battery Life	Use Dependent	Rate Dependent	Rate Dependent	Rate Dependent
FCC, IC, &/or CE Certified	√	√	√	√
IP Rating	IP67/IP64/IP65***	IP65	IP65	IP65
<b>Data Storage</b>				
Cloud				√
Local Server			√	
Mobile Device		√		
Handheld Meter	√			
<b>Interface</b>				
Desktop/Laptop	√		√	√
Mobile App		√		
Handheld Meter	√			
<b>Other</b>				
Software License			√	
Optional Cellular Subscription				√
Internet/WiFi/LAN Required			√	√
Collection Server Required			√	√
Site Survey Required			√	√

\*In Broadcast Mode Only \*\*0.1ms Available on ServiceMaster+ \*\*\*Varies with Handmeters

