

## State-of-the-Art Coupler Features Rigid Mounting and Connect/Disconnect Under Pressure



The Pioneer 0312-001 rigid mount coupler features a patented design that permits connection while both the coupler and male tip are under pressure.

These couplers can be mounted directly to a valve or rigid tubing, eliminating the need for hose assemblies and break-away clamps.

- Easy push/pull connection and disconnection under system pressure.
- Enclosed outer housing prevents dust and dirt build up.
- This coupler accepts all Pioneer 8010 Series or ISO 5675 male tips.
- Environmentally friendly Chromium 6 Free plating for excellent corrosion resistance

### Ordering Information

The 0312-001 is available in two packaging formats. Available in packages of five, or individually in the Valu-Pak clam shell for retail displays.

This coupler is the same product as **Kubota 3A111-82011**.

### Specifications

Body Size	Part Number	Thread	Pressure Rating (psi)
1/2	0312-001	7/8-14UNF-2B	3000 PSI
1/2	VP0312-001-CS	7/8-14UNF-2B	3000 PSI

