



Parker Hannifin Corporation
Industrial Hose Division
30242 Lakeland Boulevard
Wickliffe, OH 44092-1747
Telephone: (440) 833-2120
Fax: (440) 833-2230
www.safehose.com

PRODUCT UPDATE

Series SS122 Water Jetting Hose

Working Pressure and Dimensional Updates



Due to changes in manufacturing methods and processes:

- SS122-4000 is now rated to 500 psi (34.5 bar) working pressure (formerly 300 psi/20.7 bar).
- Some dimensions have changed (see table on page 2).

(Continued on page 2)

If there are any questions please contact
Parker Customer Service toll-free at:

866.810.HOSE (4673)
Eastern USA

800.242.HOSE (4673)
Western USA





Series SS122 Water Jetting Hose *Working Pressure and Dimensional Updates*

Brand Method NEW: Black text on blue stripe
PREVIOUS: White text on blue stripe

Part Number	ID (in)	ID (mm)	Reinf Plies	OD (in)	OD (mm)	Approx Wt (lbs/ft)	Approx Wt (kg/ft)	Max WP (psi)	Max WP (bar)
New									
SS122-1250	1-1/4	31.8	2	1.72	44	0.52	0.24	500	34.5
SS122-1500	1-1/2	38.1	2	1.97	50	0.63	0.29	500	34.5
SS122-2000	2	50.8	2	2.48	63	0.82	0.37	500	34.5
SS122-2500	2-1/2	63.5	4	3.10	79	1.28	0.58	500	34.5
SS122-3000	3	76.2	4	3.65	93	1.59	0.72	500	34.5
SS122-4000	4	101.6	4	4.66	118	2.10	0.95	500	34.5
Previous									
SS122-1250	1-1/4	31.8	2	1.69	43	0.49	0.22	500	34.5
SS122-1500	1-1/2	38.1	2	1.94	49	0.60	0.27	500	34.5
SS122-2000	2	50.8	2	2.50	64	0.96	0.44	500	34.5
SS122-2500	2-1/2	63.5	2	3.00	76	1.15	0.52	500	34.5
SS122-3000	3	76.2	2	3.50	89	1.36	0.62	500	34.5
SS122-4000	4	101.6	2	4.50	114	1.75	0.79	300	20.7

© 2018 Parker Hannifin Corporation. Information and specifications subject to change without notice and without liability therefor. Trademarks used herein are the property of their respective owners.