



## Sales Advisory

Parker Hannifin Corporation  
Industrial Hose Division  
30242 Lakeland Boulevard  
Wickliffe, OH 44092-1747  
Telephone: (440) 833-2120  
Fax: (440) 833-2230  
www.safehose.com



### NEW PRODUCT

#### Series 7331/7331XT

*Wildcatter® Multipurpose Fracking Hose - 6" I.D.*



Series 7331/7331XT is a high pressure oilfield stimulation/fracking suction and discharge hose designed to handle oil and refined fuels such as biodiesel (to B20 in dedicated service), diesel, ethanol and gasoline, as well as brine, mild chemicals, fracking fluids, drilling mud, petroleum waste, slurries and water. The heavy duty multipurpose hose construction provides an extended service life in multiple applications, and incorporates a wire helix that provides full suction capability, kink resistance, flexibility for ease of handling and a path to conduct a static electrical charge to ground.

Series 7331XT features a layer of ultra high molecular weight polyethylene (UHMWPE) bonded to the oil and weather resistant cover, for extreme abrasion resistance and service life.

**NOTE:** Refer to the Safety and Technical section of Catalog 4800 for safety, handling and use information. Refer to the Chemical Guide section of Catalog 4800 to determine compatibility with specific chemicals. Contact Parker for additional chemical compatibility information.

The Wildcatter trade name indicates the product is designed and manufactured for premium service in oilfield applications. However, Wildcatter products may be used in other industries, markets and applications where the product meets the required performance criteria.

*(Continued on page 2)*

If there are any questions please contact  
Parker Customer Service toll-free at:

866.810.HOSE (4673)  
Eastern USA

800.242.HOSE (4673)  
Western USA



© 2017 Parker Hannifin Corporation. Information and specifications subject to change without notice and without liability therefor.  
Trademarks used herein are the property of their respective owners.

PA 2018.02.004 Series 7331/7331XT Wildcatter Hose

ENGINEERING YOUR SUCCESS.



Parker Hannifin Corporation  
Industrial Hose Division

## Series 7331/7331XT Wildcatter® Multipurpose Fracking Hose - 6" I.D.

- Tube:** Black nitrile; ARPM Class A oil resistant
- Reinforcement:** Multiple textile plies with one wire helix
- Cover:** Black nitrile blend; 7331XT: sleek UHMWPE abrasion resistant finish
- Temp Range:** -40°F to +200°F (-40°C to +93°C)
- Brand Method:** Blue text on yellow stripe
- Brand Example:** PARKER ~~WILDCATTER~~ (7331) (7331XT) SUCTION HOSE 400 PSI
- Design Factor:** 4:1
- Industry Standards:** None applicable
- Applications:**
- Biodiesel (to B20 in dedicated service), diesel, ethanol, gasoline, oil
  - Brine, mild chemicals, fracking fluids, drilling mud, petroleum waste, slurries, water
  - General industrial
- Vacuum:** Full
- Packaging:** Coils

### Crimp Specifications

For currently qualified crimp specifications including coupling designation, refer to CrimpSource at [www.safehose.com](http://www.safehose.com).  
Refer to the COS-K4 crimper for crimp specs for hose 4" ID and smaller. Refer to the COS-K6 or COS-K10 crimpers for hose IDs larger than 4".

Part Number	ID (in)	ID (mm)	Reinf Plies	OD (in)	OD (mm)	Approx Wt (lbs/ft)	Approx Wt (kg/ft)	Min Bend Rad (in)	Min Bend Rad (mm)	Max Rec WP (psi)	Max Rec WP (bar)	Perm Cplg Rec *	Std Pack Qty (ft)	Stock Status **
7331-6000	6	152.4	6	7.047	179.0	7.65	3.47	36.0	914.4	400	27.6	*	100	N
7331XT-6000	6	152.4	6	7.060	179.3	7.08	3.21	36.0	914.4	400	27.6	*	100	N

\* **Couplings:** Refer to CrimpSource at [www.safehose.com](http://www.safehose.com) for coupling recommendations and crimp specifications.

\*\* **Stock:** "Y" indicates stocked item; "N" indicates non-stocked item. Stock status subject to change. Contact Parker Customer Service.

**⚠ WARNING!** Couplings attached with bands or clamps may reduce the working pressure of the hose assembly to less than the maximum rated working pressure of the hose. Refer to the NAHAD Industrial Hose Assembly Guidelines.