

Fact Sheet

Visolite Inspection High Intensity LED Black Light

Powerful, rechargeable, high-intensity UV-A fluorescent leak detection inspection lamp featuring state-of-the-art, ultra-high flux LED technology.

- Powerful. Four times brighter than most corded, high-intensity UV lamps. Ultra-high intensity of up to 50,000 $\mu\text{W}/\text{cm}^2$ of true UV-A (365 nm)
- Inspection range of up to 25 feet (7.6 m)
- Instant-on Operation. Push the button and the lamp immediately reaches full power and is ready for use. Eliminates down time waiting for bulbs to warm up
- Cordless. Use it anywhere
- Rechargeable — Powered by a rechargeable NiMH battery. Provides 90 minutes of continuous inspection between charges (AC and DC chargers included)
- Long Life — 100,000-hour LED bulb. Electronic Intensity Stabilizer ensures consistent performance. Beam strength will not fade between charges
- Versatile — Meets MIL and ASTM specs for FPI and MPI. 100,000-hour LED service life
- Ergonomic, portable and rugged. Anodized aluminum lamp body minimizes corrosion and stands up to years of heavy use
- Low visible light emission-- less than 2 foot-candles (22 lux)
- Indicator lights for battery strength and charge status



365 UV-A LED Inspection Flashlight (Patent Pending)



Specifications

Lamp Head Diameter 2 in (5.1 cm)

Length 8 in (20.3 cm) Weight (with battery) 11.8 oz (335 g)

Power Requirement 3.6V, 2AH NiMH internal battery stick (rechargeable)