


Specifications	Description
<b>Security</b>	
Security	TPM module
<b>Software</b>	
OS	Secured Embedded Linux
Applications	Parker Voice of the Machine Edge software
<b>Power</b>	
Input	DC12 / 24V(9-36V), Locked Power Jack
Consumption	6W (Pulse8W), Sleep 2W. (without LTE,GPS,WLAN)
<b>Mechanical</b>	
Dimensions	176x101x52mm (Box)
Install Brackets	198x101x52mm
Weight	0.6Kg (1.2Kg package Kit)
Enclosure	Aluminum Alloy with Black Color
<b>Environment Condition</b>	
Temperature	Operating: -20°C ~ +60°C, Storage:-40°C ~ +85°C
Humidity	5-95%RH at 25-35 (Non-Condensation)
Cooling Mode	Fan less, Heat Sink
Approvals	UL, FCC Class B, CE, RoHS, and PTCRB Compliance

## Repeater



- Primary use as network repeater [range extender] for all sensors joined to gateway receiver
- Support for up to 250 sensors at one hop each
- Robust overmolded design for harsh environments

Part Number	W	D	H	L
SNREN-2	2.75" [70mm]	1.81" [46mm]	.53" [13mm]	3.12" [79mm]



**WARNING**

The products listed can expose you to chemicals including Lead, which is known to the State of California to cause cancer, and to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

