



Parker Hannifin Corporation  
Industrial Hose Division  
30242 Lakeland Boulevard  
Wickliffe, OH 44092-1747  
Telephone: (440) 833-2120  
Fax: (440) 833-2230  
www.safehose.com

## PRODUCT UPDATE

### Series 7308 Hose – Obsolete

### *Series 7308E MAXIFLEX® Lightweight Air Hose – Suggested Replacement*



The Parker Maxiflex Lightweight Air Hose product offering is being upgraded and consolidated into Series 7308E. All sizes of Series 7308E are rated to 300 psi maximum working pressure.

Series 7308E is a flexible, lightweight, medium pressure hose designed to handle air—including light oil lubricating mists found in air tool lubricating systems—mild chemicals and water. The rugged cover is resistant to abrasion and weathering. Series 7308E provides service for low to medium pressure air and water applications in construction, general industrial, mines and quarries.

Series 7308 is now obsolete and no longer available. Refer to the table on page 2 for a product comparison.

*(Continued on page 2)*

If there are any questions please contact  
Parker Customer Service toll-free at:

866.810.HOSE (4673)  
Eastern USA

800.242.HOSE (4673)  
Western USA



© 2018 Parker Hannifin Corporation. Information and specifications subject to change without notice and without liability therefor.  
Trademarks used herein are the property of their respective owners.

PA 2018.03.010 Series 7308-7308E

ENGINEERING YOUR SUCCESS.



Parker Hannifin Corporation  
Industrial Hose Division

## Series 7308 Hose – Obsolete

### Series 7308E MAXIFLEX® Lightweight Air Hose – Suggested Replacement

- Tube:** Black SBR
- Reinforcement:** Multiple textile plies
- Cover:** Yellow SBR; wrapped finish
- Temp Range:** -20°F to +212°F (-29°C to +100°C)
- Brand Method:** Embossed
- Brand Example:** PARKER SERIES 7308E MAXIFLEX AIR HOSE 300 PSI WP
- Design Factor:** 3:1
- Industry Standards:** None applicable
- Applications:**
  - Air, water
  - Heavy duty air tools, air compressors
  - Construction, general industrial, mines, quarries

#### Crimp Specifications

For currently qualified crimp specifications including coupling designation, refer to CrimpSource at [www.safehose.com](http://www.safehose.com). Refer to the COS-K4 crimper for crimp specs for hose 4" ID and smaller. Refer to the COS-K6 or COS-K10 crimpers for hose IDs larger than 4".

Part Number	ID (in)	ID (mm)	Reinf Plies	OD (in)	OD (mm)	Approx Wt (lbs/ft)	Approx Wt (kg/ft)	Max Rec WP (psi)	Max Rec WP (bar)	Vacuum (in/Hg)	Std Pack Qty (ft)	Pkg Type
<b>New Part Number</b>												
7308E-1000300	1	25.4	2	1.5	38.1	0.5	0.8	300	21	n/a	100	Coil
7308E-1250300	1-1/4	31.8	2	1.7	43.2	0.6	0.9	300	21	n/a	100	Coil
7308E-1500300	1-1/2	38.1	2	2.1	53.3	0.9	1.3	300	21	n/a	100	Coil
7308E-2000300	2	50.8	4	2.6	66.0	1.2	1.7	300	21	n/a	100	Coil
7308E-2500300	2-1/2	63.5	4	3.1	78.7	1.4	2.1	300	21	n/a	100	Coil
7308E-3000300	3	76.2	4	3.6	91.4	1.7	2.5	300	21	n/a	100	Coil
<b>Obsolete Part Number</b>												
7308-1004	1	25.4	2	1.5	38.1	0.5	0.7	250	17	n/a	100	Coil
7308-1254	1-1/4	31.8	2	1.8	45.7	0.6	0.9	250	17	n/a	100	Coil
7208-1504	1-1/2	38.1	2	2.0	50.8	0.7	1.1	250	17	n/a	100	Coil
7308-2004	2	50.8	4	2.6	66.0	1.1	1.6	250	17	n/a	100	Coil
7308-2504	2-1/2	63.5	4	3.1	78.7	1.2	1.8	250	17	n/a	100	Coil
7308-3004	3	76.2	4	3.5	88.9	1.4	2.1	250	17	n/a	100	Coil

**⚠ WARNING!** Couplings attached with bands or clamps may reduce the working pressure of the hose assembly to less than the maximum rated working pressure of the hose. Refer to the NAHAD Industrial Hose Assembly Guidelines.