



Parker Hannifin Corporation  
Industrial Hose Division  
30242 Lakeland Boulevard  
Wickliffe, OH 44092-1747  
Telephone: (440) 833-2120  
Fax: (440) 833-2230  
www.safehose.com

**NEW PRODUCT**

**Series 7200LB Large Bore Hydrocarbon Drain Hose**  
*New Series Complements Series 7200*



Series 7200LB is a large bore hydrocarbon drain hose designed to quickly evacuate large volumes of hot, liquefied residue from steam-cleaning operations in manufacturing and processing plants, and refineries. The high-temperature, oil-resistant tube and cover withstand attack by steam vapors and petroleum-based runoff. The hose construction incorporates a static wire as a path to conduct an electrical charge to ground. The vivid blue chloroprene cover is resistant to oil and weathering, and provides color-coded identification. Series 7200LB is qualified with crimp couplings for easy and quick assembly fabrication as well as maintenance-free service.

Series 7200LB complements the existing hydrocarbon drain hose offering. The following is a high-level comparison between new Series 7200LB and the continuing Series 7200 hydrocarbon drain hoses:

	<b>Series 7200LB</b>	<b>Series 7200</b>
• Size Range	2" & 4" ID	3/4" & 1" ID
• Reinforcement	textile plies w/static wire	wire braid
• Max WP	300 psi	350 psi
• Max Temp	300° - 350°F	350°F
• Design Factor	3:1	4:1

**NOTE:** Do not use Series 7200 or 7200LB for steam service.

*(Continued on page 2)*

If there are any questions please contact  
Parker Customer Service toll-free at:

866.810.HOSE (4673)  
Eastern USA

800.242.HOSE (4673)  
Western USA



© 2018 Parker Hannifin Corporation. Information and specifications subject to change without notice and without liability therefor.  
Trademarks used herein are the property of their respective owners.

PA 2018.03.009 Series 7200LB



Parker Hannifin Corporation  
Industrial Hose Division

## Series 7200LB Large Bore Hydrocarbon Drain Hose

### *New Series Complements Series 7200*

- Tube:** Black nitrile
- Reinforcement:** Multiple textile plies with static wire
- Cover:** Blue chloroprene
- Temp Range:** -20°F to +300°F continuous/+350°F intermittent  
(-29°C to +149°C continuous/+177°C intermittent)
- Brand Method:** Blue text on green stripe
- Brand Example:** PARKER SERIES 7200LB HYDROCARBON DRAIN HOSE 300 PSI 300°F
- Design Factor:** 3:1
- Industry Standards:** None applicable
- Applications:**
- Drainage of hot residue from steam-cleaning operations
  - Manufacturing and processing plants, refineries

#### Crimp Specifications

For currently qualified crimp specifications including coupling designation, refer to CrimpSource at [www.safehose.com](http://www.safehose.com).  
Refer to the COS-K4 crimper for crimp specs for hose 4" ID and smaller. Refer to the COS-K6 or COS-K10 crimpers for hose IDs larger than 4".

Part Number	ID (in)	ID (mm)	Reinf Plies	OD (in)	OD (mm)	Approx Wt (lbs/ft)	Approx Wt (kg/ft)	Max Rec WP (psi)	Max Rec WP (bar)	Vacuum (in/Hg)	Std Pack Qty (ft)	Pkg Type
7200LB-2000	2	50.8	2	2.7	67.6	1.3	1.9	300	21	n/a	100	Coil
7200LB-4000	4	101.6	4	4.7	122.0	2.9	4.3	300	21	n/a	100	Coil

**⚠ WARNING!** Couplings attached with bands or clamps may reduce the working pressure of the hose assembly to less than the maximum rated working pressure of the hose. Refer to the NAHAD Industrial Hose Assembly Guidelines.