
Table of Contents

Hydraulic Maintenance Introduction

Hydraulic Maintenance	1-1
Typical Hydraulic Circuit Schematic	1-1
Principles of Diagnosis and Testing	1-1
Take Nothing for Granted	1-2
Keep Your Hands in Your Pocket	1-2
Know the System	1-3
Visually Inspect the Machine.	1-3
Operate the Machine	1-3
Check All Services to the Machine	1-3
Isolate Legs of the Circuit - Avoid Open Lines	1-3
Identify the Problem	1-4
Match the Problem to the Cause	1-4
Reach a Conclusion	1-4
Test Your Conclusion	1-4
Report Your Findings	1-5
Repair and/or Replace Components as Necessary	1-5
Review	1-5

Hydraulic Graphic Symbolology

General Symbols	2-1
General Characteristics of Symbols	2-2
Lines	2-3
Circles, Semi-Circles, Squares, Rectangles and Diamonds	2-3
Miscellaneous Symbols	2-4
Energy Conversion Components	2-4
Pumps	2-4
Motors	2-5
Pump-Motor Units	2-5
Cylinders	2-5
Single-Acting Cylinders	2-5
Double-Acting Cylinders	2-6
Differential Cylinders and Cylinders with Cushions	2-6
Telescopic Cylinders	2-6
Pressure Intensifier	2-6
Control Valves	2-6
Flow Paths	2-7
Directional Control Valve Designations 2/2 or 3/2	2-7
4/2 Directional Valve	2-8
4/3 Directional Valve	2-8
4/3 or 4/4 Mobile Directional Valves	2-9
Throttling Directional Control	2-9
Electrohydraulic Servo Valve	2-9
Non-Return Valves - Check Valves	2-9
Shuttle Valves	2-10
Pressure Control Valves	2-10
Pressure Relief Valves	2-10
Proportional Relief Valve	2-10
Sequence Valve	2-11
Pressure Reducing Valve	2-11
Regulator Valve	2-11
Flow Control Valves	2-12
Flow Divider Valve	2-12
Shut-off Valve	2-12
Source of Pressure	2-13

Prime Movers and Power Take-offs	2-13
Flow Lines	2-13
Quick Couplings	2-14
Rotary Connection	2-14
Reservoirs	2-14
Accumulators	2-14
Fluid Conditioners, Filters and Heat Exchangers	2-14
Mechanical Components	2-15
Actuator Methods	2-15
Manual Controls	2-16
Mechanical Controls	2-16
Electrical Controls	2-16
Pressure Controls	2-16
Combined Controls	2-17
Miscellaneous Equipment	2-17
Mechanical Feedback Control	2-17
Exercise - Hydraulic Graphic Symbology	2-18

Power Unit Maintenance

Hydraulic Reservoir	3-1
Reservoir Construction	3-1
Component Mounting	3-1
Reservoir Add-ons	3-1
Reservoir Interior	3-2
Electric Motors	3-2
3-Phase Squirrel Cage Induction Motor	3-2
NEMA Speed Rating	3-2
Motor Enclosure Type	3-3
NEMA Frame Size	3-3
Electric Motor and Pump Coupling	3-4
Rigid Coupling	3-4
Flexible Coupling	3-4
Shaft Alignment	3-4
Dial Indicator Installation	3-4
Shimming Requirements	3-4
Shaft End-play Clearance	3-5
When are Alignment Checks Required?	3-5
Pump Mounting	3-5
Mounting Base Plate	3-5
Start-up Procedure	3-6
Noise	3-7
How We Hear Internal Noise from a Hydraulic System	3-7
Noise in the Hydraulic Pump	3-7
How Pressure Ripples Generate Noise	3-8
Other Noises Generated by the Pump	3-8
Violent Changes in Fluid Velocity Make Noise	3-8
Aeration and Cavitation Cause Noise	3-9
Noise from Pressure Control Valves	3-9
Other Noises Associated with the Power Unit	3-9
Sources of Noise Generation	3-9
The Electrical Motor Contributes Much to the Overall System Noise	3-10
Noise from the Motor Cooling Fan	3-10
Noise from the Coupling	3-10
Most Common Causes of Noise	3-10
Some Simple Ways to Reduce Operating Noise	3-11
Reducing the Decibel Level of the Power Unit	3-12
Lowering Noise Generationed from the Manufacturer	3-14

Isolating the Noise	3-14
Dampening Noise	3-14
Hydraulic Acoustic Filter	3-17
Power Unit Enclosures - "Dog Houses"	3-17
When to Use a "Dog House"	3-18
Isolation Room for Power Unit	3-19
Other Major Areas of Noise Reduction	3-19

Pump Maintenance

Hydrodynamics and Hydrostatic Pumps	4-1
Gear Pumps	4-1
External Gear Pumps	4-1
How an External Gear Pump Works	4-2
Internal Gear Pump	4-2
How an Internal Gear Pump Works	4-2
Lobe Pump	4-2
Screw Pump	4-2
How a Screw Pump Works	4-2
Vane Pumps	4-2
What a Fixed Displacement Vane Consists Of	4-2
How a Fixed Displacement Vane Pump Works	4-3
Pressure Compensated Variable Volume Vane Pump Consists Of	4-3
How Variable Volume Works	4-3
How Pressure Compensation Works	4-3
Spool Compensators	4-4
How Spool Compensation works	4-4
Pilot Operated Pressure Compensation	4-4
Piston Pumps	4-4
What a Fixed Displacement In-line Piston Pump Consists Of	4-5
What a Fixed Displacement Bent-axis Piston Pump Consists Of	4-5
How a Bent-axis Piston Pump Works	4-5
Radial Piston Pump	4-5
Variable Volume Piston Pumps	4-5
How the Variable Volume Adjustment Works	4-5
Pressure Compensated Variable Piston Pump	4-6
How Pressure Compensation Works	4-6
Load Sensing	4-6
How Load Sensing Works	4-7
Pump Performance	4-7
Cavitation	4-7
Indication of Cavitation	4-8
Entrained Air	4-8
Indication of Entrained Air	4-8
Troubleshooting Pumps	4-8
Hydraulic Fluid	4-8
Pump Wear Due to Contaminated Fluid	4-9
Typical Abrasive Wear	4-9
Effects of Varnish and Sludge	4-9
Effects of Improper Fluid	4-9
Exceeding Pump Design Limits	4-10
Troubleshooting Charts	4-11

Pressure Control Valve Maintenance

Relief Valve 5-1
 Override Characteristics of Relief Valves 5-1
 Unloading Relief Valve 5-2
 Sequence Valve 5-2
 Counterbalance Valve 5-2
 Brake Valve 5-2
 Pressure Reducing Valve 5-3
 Solenoid Operated Pressure Control Valves 5-3
 Single Pressure with Remote Pilot Adjustment 5-3
 Bi-pressure and Tri-pressure Solenoid Operated Relief Valves 5-3
 Remote Pilot Adjustment 5-4
 Generalizations About Pressure Control Valves 5-4
 Troubleshooting Pressure Control Valves 5-8

Directional Control Valve Maintenance

3-position Center Conditions 6-1
 Open Center Condition 6-1
 Closed Center Condition 6-1
 Float Center Condition 6-1
 Tandem Center Condition 6-2
 Directional Valve Actuators 6-2
 Solenoid Actuators 6-2
 Air Gap Solenoid 6-2
 How an Air Gap Solenoid Works 6-2
 Wet Armature Solenoid 6-3
 What a Wet Armature Solenoid Consists Of 6-3
 How a Wet Armature Solenoid Works 6-3
 AC Hum 6-3
 Shading Coils 6-3
 Eddy Currents 6-3
 Solenoid Inrush Current 6-4
 Continuous Duty Solenoid 6-4
 Manual Override 6-4
 Troubleshooting Solenoids 6-5
 Solenoid Blockage 6-5
 Low Voltage 6-5
 Excessive Cycling Rate 6-6
 Other Burnout Causes 6-6
 Match Force to Load 6-6
 General Tips 6-6
 Solenoid Limitations 6-7
 Electrohydraulic Directional Flow Control Valves 6-7
 Proportional vs. Servo 6-7
 Response 6-7
 Spool Center Condition 6-7
 Filtration Requirements 6-8
 Proportional Valve Construction 6-8
 How a Direct Operated Proportional Solenoid Directional Valve Works 6-8
 How a Pilot Operated Proportional Solenoid Controlled Directional Valve Works 6-8
 A Pressure Differential Proportional Directional Valve 6-9
 First Stage Pilot Valve Consists Of 6-9
 2nd Stage Main Slave Consists Of 6-9
 How the Pilot Valve Works 6-9
 How the Main Valve Works 6-9
 What a Servo Valve Consists Of 6-9
 Types of First Stages 6-9

Types of 2nd Stage Spool Designs	6-10
Line-to-Line Condition	6-10
Underlapped Condition	6-10
Overlapped Condition	6-10
How a Servo Valve Works	6-10
Troubleshooting Directional Control Valves	6-11

Flow Control Valve & Check Valve Maintenance

Needle Valve	7-1
Pressure Differential	7-2
Pressure Compensated Flow Control Valves	7-2
Restrictor Type Pressure Compensated Flow Control Valve	7-2
How a Restrictor Type Pressure Compensated Flow Control Valve Works	7-2
A Bypass Type Pressure Compensated Flow Control Valve	7-3
How a Bypass Type Pressure Compensated Flow Control Valve Works	7-3
Temperature Affects Flow	7-4
Temperature Compensation with a Sharp Edge Orifice	7-4
Temperature-Pressure Compensated Flow Control Valve	7-5
Lunge Control	7-5
Setting the Lunge Control Adjustment	7-5
Acceleration and Deceleration Flow Control Valves	7-6
Pilot Operated Flow Control Valves	7-6
Reverse Flow Through a Flow Control Valve	7-7
Check Valves	7-7
Simple and 90° Checks	7-7
Pilot Operated Check	7-8
Double Pilot Operated Check Valve	7-8
Adjustable Check Valves	7-8
Troubleshooting Flow Control and Check Valves	7-9

Cylinders, Motors and Accumulator Maintenance

What a Cylinder Consists Of	8-1
Piston Seal Leakage	8-1
Effects of Piston Leakage	8-1
Intensification from Piston Leakage	8-2
Checking for Piston Seal Leakage	8-2
Intensification at Cylinder Rod Side	8-3
Cylinder Troubleshooting	8-5
Hydraulic Motors Types	8-8
Gear Motor	8-8
Vane Motor	8-8
Axial Piston Motor	8-9
Motor Cavitation	8-10
Make-up Check Valves	8-10
Crossover Relief Valves	8-11
Hydraulic Motor Wear	8-11
Check for Hydraulic Motor Wear	8-12
Accumulator Types	8-16
Weight-loaded Accumulator	8-16
Spring-loaded Accumulator	8-16
Hydro-pneumatic Accumulator	8-17
Piston Type Accumulator	8-18
Diaphragm Type accumulator	8-18
Bladder Type Accumulator	8-18
Precharge	8-19
Precharge Affects Shock Absorber Operation	8-19
Losing Gas Precharge	8-20

Checking Gas Precharge	8-20
Accumulator Troubleshooting	8-22
Caution when Disassembling Accumulator	8-22

Leakage Elimination in Hydraulic Systems

Leakage Occurs as a Result Of	9-1
System Design Component Selection-Fitting Style	9-1
37° Flare	9-1
Flareless	9-1
Multiple Bite Flareless	9-2
Face Seal with O-ring	9-2
Pipe Thread Port Connections	9-2
Straight Thread with O-ring	9-2
4-bolt Split Flange	9-2
Component Selection - Tube type	9-2
Component Interchangeability	9-3
System Design - Routing	9-3
Avoid Excessive Strain	9-3
Use Proper Clamping	9-3
Allow for Motion Under Load	9-3
Component Quality - Fitting Quality	9-4
Tubing Quality	9-4
Mating Parts Quality	9-4
Installation - Tube Bends	9-4
Cut Tubing Square	9-4
Tube Flaring	9-4
Under and Overflaring	9-4
Flareless Preset	9-5
Improper Flareless Preset	9-5
Face Seal Brazing	9-5
Improper Brazing	9-5
Assembly of Tube to 37° Flare fitting - Torque Method	9-5
Assembly of Mixed Platings on 37° Flare Fitting	9-6
Assembly of Tube of 37° Flared Fitting Flat Method	9-6
Flats from Finger Tight (FFFT) Table	9-6
Torque and FFFT Methods Compared	9-6
Assembly of Flareless Fitting	9-6
Assembly of Face Seal Fitting	9-7
Assembly of Pipe Thread Fitting to Port	9-7
Assembly of Straight Thread Fitting to Port	9-7
Assembly of Adjustable Straight Thread Fitting	9-7
Pinched O-rings	9-7
Assembly of 4-bolt Split Flange Fitting to Port	9-7
4-bolt Split Flange Torque Table	9-8
Troubleshooting Fitting Failures	9-8
Abuse Failures	9-8
Recommendations for Leak Free Systems	9-11

Fluids and Filter Maintenance

Petroleum-Base Fluid Additives	10-2
Oil Problems	10-3
High Pressure Lubrication	10-3
Check for High Pressure Lubrication	10-3
Oil Oxidation	10-3
Check for Oxidized Oil	10-4
Water in Hydraulic Oil	10-5
Check for Water in Hydraulic Oil	10-5

Foaming	10-5
Check for Foaming	10-6
Dirt in Oil	10-6
Check for Dirt in Oil	10-6
Fire Resistant Hydraulic Fluid	10-7
Water Base Fluid	10-7
Problems with Water Base Fluid	10-8
Phase Separation	10-8
Check for Phase Separation	10-9
Bacteria Formation	10-9
Check for Bacteria Formation	10-9
Water Evaporation	10-9
Synthetic Fire Resistant Fluid	10-10
Problems Related to all Fire Resistant Fluids	10-10
Compatibility Problem	10-10
Foaming and Air Retention	10-11
Dirt Retention	10-11
Fluid Maintenance Considerations	10-11
Maintaining Proper Fluid Temperature	10-13
How Hot is "Too Hot"	10-13
Measuring Fluid Temperature	10-13
Isolating Trouble Spots	10-14
Preventive Measures	10-14
Troubleshooting	10-16
Fluid Sampling Procedures	10-17
For Systems with a Sampling Valve	10-17
Systems without a Sampling Valve	10-18
In the Tank Sampling	10-18
In-line Sampling	10-18
Filtration	10-20
Types of Filter Media	10-20
Depth Filter Media	10-21
Surface Filter Media	10-21
What Filter Media to Use	10-21
Depth Type Filter - Advantages and Disadvantages	10-21
Surface Type Filter - Advantages and Disadvantages	10-22
Filter Installation	10-22
Suction Filter and Strainer Characteristics	10-22
Suction Filter and Straining Considerations	10-23
Pressure Filter Installation and Characteristics	10-23
Pressure Filter Considerations	10-23
Return Line filter Installation and Characteristics	10-24
Return Line Filter Considerations	10-24
Off-line or Side Stream Filter Installation	10-25
Off-line or Side Stream Filtering Considerations	10-25
Filters Must be Maintained	10-25
Maintenance Suggestions	10-26
Troubleshooting Filters	10-27
Preventive Maintenance Points to Remember	10-29