

# Product Highlight

## BHA® Vacutrans™ Vacuum System

### The Vacutrans™ Vacuum Cleaning System Powerful Enough To Pick Up Large Pieces Of Material!

Vacutrans™ is a specially designed industrial/contractor's tool made to convert your compressed air supply into a high powered vacuum and material transferring system. The Vacutrans can pickup and convey powders, plastic pellets, grain, sand, abrasives, aggregates, liquids and numerous other bulk materials in both clean up and material transfer functions. It can also convert to a shop-vac, and be used to inject BHA Neutralite® precoat or BHA Visolite® Leak Detection powder.

The Vacutrans is a portable system that's easy to use and capable of providing the performance of larger systems. It works on most fabric filter collectors and is adaptable for use on electrostatic precipitator penthouses and high voltage compartments.

#### Features

- Reduced Maintenance Time
- Proven Extended Bag Life
- Easy to Use
- Easy Installation
- Maintenance Free
- Portable


#### Benefits

- Provides quick, easy cleanup.
- Reduces abrasion on the clean side of the fabric filter by eliminating particulate buildup in the clean air plenum.
- No manual dust handling. Dust flows directly into the collector's hopper, eliminating the need to remove the bags for cleanup.
- Simply attach the Vacutrans to the discharge hose and connect air.
- Has no moving parts to lubricate or wear.
- Moves easily between compartments or collectors. Entire unit weighs 142 pounds.

The Vacutrans System operates in the 150 CFM range at 100 psi\* and comes complete with:


- Vacutrans powered unit
- Discharge hose attachment
- One 2 in. x 25 ft. pickup hose
- Two 3 in. x 25 ft. discharge hoses
- One 3 in. hose mender

\*Note: Can operate as low as 60 psi.



# Product Highlight

## BHA® Vacutrans™ Vacuum System



Total Assembled Length to Nipple: Approx. 28"

### Vacutrans Package P/N: 825-0009

#### Includes:

- 1 - Vacutrans V-150
- 1 - Discharge Hose Attachment
- 1 - 25' x 2" Pickup Hose
- 2 - 25' x 3" Discharge Hose
- 1 - 3" Hose Mender

