



New and Improved Wet line Kits

Ordering Made Easy

aerospace
climate control
electromechanical
filtration
fluid & gas handling
hydraulics
pneumatics
process control
sealing & shielding



ENGINEERING YOUR SUCCESS.

Selecting Your System

With the development of eConfigurator™ Parker, you can select the components your fleet wants for the following systems. Dump Trucks - Dump Trailers - Moving Floors- Low Boy Trailers - Live Bottom Trailers - Combination Dump Trailer Low Boy - Combination Dump Trailer - Moving Floor- Low Boy & More - PTO IMPROVEMENT - now you can select a different PTO speed within the e-Configurator

Parker wetline kits and PTOs are shipped within 48 hours, and are ready for immediate installation. Step by Step prints are provided for your installer to make the installation quick and easy. Packing for the wetline kit comes in a single box, PTO is shipped separately and includes all your selected components based upon your application.

Advantages

- No guesswork in Power Take-Off (P.T.O.) or other component selection.....Less chance for system error.
- No time wasted in parts collatingQuick order entry.
- No need for multiple suppliers.....Reduce invoices, single order entry point.
- Genuine Chelsea P.T.O.s, Commercial Dump Pumps and Parker Hose & Fittings.....Market accepted name & quality.
- In Stock.....Quick delivery.

Benefits

Parker Wet Line System

- High pressure hose with J.I.C. swivel fitting for quick and easy installation.
- Improved Filtration - New coreless filtration is designed to handle the extra flow surge and pressure demand for Dump Truck and Trailer applications to prevent filter blow off.
- Extra long hose kits are available for special applications.
- Three line systems are recommended to protect pump from becoming over heated.

Chelsea®

- Power Take-Offs available for Automatic and Manual Transmissions.
- Over Seven Shift Options With 5 Consoles.

Parker

- C101/C102 dump pumps.
Direct mount or remote mount.
Optional air or cable shift.
- Improved Filtration for all applications
Mounting bracket and hardware included.
Guage Standard.
10 micron coreless spin on filter.
- Swivel fittings at all connections for quick and easy installation.

Also Available:

Shut-Off Valves

- Ball valves 1-1/4", 1-1/2".
- Extra heavy duty nipple to connect valves to tank.

Tanks

- Aluminum, steel and polyethylene tanks.
- Upright or side mount complete with mounting kit.
- Sight gauge.

**www.phtruck.com/wetlinkits
And Configure Your Kit Today**

